




D




SECTION X-X



- 1 AMP, DATE CODE, & PART NO. MARKED THIS AREA.
- 2 HOUSING MATERIAL: POLYPHENYLENE SULFIDE, GST-40F, PER MIL-M-24519.
- 3 CONTACT MATERIAL: BRASS
- 4 FINISH: .000030 GOLD OVER .000050 NICKEL IN CONTACT AREA.
- 5 FINISH: .000100 TIN LEAD OVER .000050 NICKEL.
- 6 LETTERS INDICATING OUTSIDE ROWS AND NUMBERS INDICATING END CAVITIES MARKED THIS SURFACE.
- 7 NUMBERS INDICATING EVERY FIVE CAVITIES MARKED ON BOTH SIDES.
- 8 LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE.
- 9 FINISH: .000100 TIN OVER .000050 NICKEL.

B



PC BOARD LAYOUT

9		4.900	49	5.044	5.450	5.750	150	5-531137-4
		3.400	34	3.544	3.950	4.250	105	5-531137-2
		2.900	29	3.044	3.450	3.750	90	5-531137-1
8	OBSOLETE	9.900	99	10.044	10.450	10.750	300	1-531137-5
	OBSOLETE	8.900	89	9.044	9.450	9.750	270	1-531137-4
8		6.400	64	6.544	6.950	7.250	195	1-531137-3
	OBSOLETE	4.400	44	4.544	4.950	5.250	135	1-531137-2
8	OBSOLETE	3.200	32	3.344	3.750	4.050	99	1-531137-1
	OBSOLETE	4.100	41	4.244	4.650	4.950	126	1-531137-0
8	OBSOLETE	4.000	40	4.144	4.550	4.850	123	531137-9
		7.900	79	8.044	8.450	8.750	240	531137-8
8		6.900	69	7.044	7.450	7.750	210	531137-7
	OBSOLETE	5.900	59	6.044	6.450	6.750	180	531137-6
8		5.400	54	5.544	5.950	6.250	165	531137-5
		4.900	49	5.044	5.450	5.750	150	531137-4
8		3.900	39	4.044	4.450	4.750	120	531137-3
		3.400	34	3.544	3.950	4.250	105	531137-2
8		2.900	29	3.044	3.450	3.750	90	531137-1
		E	D	C	B	A	NO. OF POSN.	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.D.KISELA 4-6-93	TE Connectivity	
DIMENSIONS: INCHES		CHK D.MILLER 5-10-93	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.MILLER 5-10-93	PRODUCT SPEC	
0.000000		APPLICATION SPEC		SIZE
1.000000		WEIGHT		CAGE CODE
2.000000		DRAWING NO		RESTRICTED TO
3.000000		000779		531137
4.000000		CUSTOMER DRAWING		SCALE
5.000000		SHEET		1 OF 1
6.000000		REV		