



Series 625 DIP Header w/Screw Machine Contacts

FEATURES

- Available in either Screw Machine or Coined Contacts in a Variety of Styles


GENERAL SPECIFICATIONS

- BODY MATERIAL:** Black UL 94V-0 Glass-filled 4/6 Nylon
- FORK & POST CONTACTS:** Brass 360 1/2-hard per UNS C36000 ASTM B16/B16M-05
- SOLDER CUP CONTACTS:** Phosphor Bronze per 544 UNS C54400 ASTM B139-01
- CONTACT PLATING:** 10μ [0.25μ] min. Au per MIL-G-45204 —OR— 200μ [5.08μ] min. 93/7 Sn/Pb per ASTM B545 or 200μ [5.08μ] min. Sn per ASTM B545 Type 1 over 100μ [2.54μ] min. Ni per SAE AMS-QQ-N-290B
- CONTACT CURRENT RATING:** 2 amps (3 amps for Pin Style 5)
- OPERATING TEMPERATURE:** -67°F to 221°F [-55°C to 105°C] for Sn & Sn/Pb plating; -67°F to 257°F [-55°C to 125°C] for Au plating
- ACCEPTS LEADS:** up to 0.035 [0.89] dia.

MOUNTING CONSIDERATIONS

- SUGGESTED PCB HOLE SIZE:** 0.028 ±0.002 [0.71 ±0.05] dia.

Centers "Y"	Dim. "Z"	Body Style	Available Sizes
0.200 [5.08]	0.300 [7.62]	A ¹	2 thru 10
0.300 [7.62]	0.400 [10.16]	CB	2 thru 20 22 thru 40
0.400 [10.16]	0.500 [12.70]	C	2 thru 22
0.600 [15.24]	0.700 [17.78]	CB	2 thru 40 42 thru 48
0.800 [20.32]	0.900 [22.86]	D ²	14 and 16
0.900 [22.86]	1.000 [25.40]	B	2 thru 64



ORDERING INFORMATION

XX-X 625-X XXX

Plating

0 = Sn
OTL = Sn/Pb
1 = Au



Pin Style
(See Drawing)

Series


Row-to-Row Spacing, Dim. "Y"

2 = 0.200 [5.08]
3 = 0.300 [7.62]
4 = 0.400 [10.16]
6 = 0.600 [15.24]
8 = 0.800 [20.32]
9 = 0.900 [22.86]


No. of Pins
(See Table)




¹ Reduced Tail Length




Body Style B




Body Style C




² Drilled FR-4




① FORK STYLE




② POST STYLE



③ SOLDER CUP



⑤ FORK WIRE WRAP



⑦ POST STYLE

ALL DIMENSIONS: INCHES [MILLIMETERS]

ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED

CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA

TEL 215-781-9956 • FAX 215-781-9845

WWW.ARIESELEC.COM • INFO@ARIESELEC.COM



12035
Rev. 6.2
1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aries Electronics:](#)

[16-6625-21](#)