


Product	Contacts: 12, female cable connector, cable outlet 6 - 8 mm, green
Area	Snap-in IP67 Series 720
Article number	99 9134 72 12


Illustration



Scale drawing



Contact Arrangement



	X	Y
1	0,00	-3,70
2	-2,62	-2,62
3	-3,70	0,00
4	-2,62	2,62
5	0,00	3,70
6	2,62	2,62
7	3,70	0,00
8	2,62	-2,62
9	1,79	-0,74
10	-0,74	-1,79
11	-1,79	0,74
12	0,74	1,79

You can find the item description on the next page.

Technical data			
Common values		Electrical values	
Connector Design	Cable socket	Rated voltage	60
Connector locking system	snap	Rated impulse voltage	800 V
Termination	solder	Pollution degree	2
Wire gauge (mm)	0,25 mm ²	Overvoltage category	II
Wire gauge (AWG)	24	Material group	II
Cable outlet	6 - 8 mm	Rated current (40°C)	2 A
Upper temperature	85 °C	Volume resistivity	≤ 3 mΩ
Lower temperature	-40 °C	EMV compliance	not shielded
		Degree of protection	IP67
		Material	
		Material of contact	CuSn (Bronze)
		Contact plating	Au (gold)
		Material of contact body	PA (UL 94 V-0)

Product	Contacts: 12, female cable connector, cable outlet 6 - 8 mm, green
Area	Snap-in IP67 Series 720
Article number	99 9134 72 12

Item description

