


Product Search

- [1.0/2.3](#)
[1.6/5.6](#)
[AFI](#)
[AMC](#)
[BNC / RP-BNC](#)
[C](#)
[FAKRA SMB](#)
[FME](#)
[HD BNC](#)
[HN](#)
[MCX](#)
[Mini BNC](#)
[Mini UHF](#)
[Mini 75 Ω SMB](#)
[MMCX](#)
[Precision \(APC\)](#)
[QMA](#)
[SC](#)
[SMA / RP-SMA](#)
[SMB](#)
[SMC](#)
[SMP](#)
[SSMB](#)
[TNC / RP-TNC](#)
[Triax](#)
[True 75 Ω BNC](#)
[Twin BNC](#)
[Twinax](#)
[Type F](#)
[Type G](#)
[Type N](#)
[UHF](#)
[Reverse Polarity](#)
-
- [Adapters](#)
[Tools](#)
[Accessories](#)
-
- [Product Search](#)
src="/images/dottedline.gif" >
[Inventory Search](#)

product details



back

Please note: Images are for reference only

Amphenol Part Number:	031-70507
Description:	75 OHM DUAL PORT BNC R/A JACK
Product Series:	BNC
Product Type:	Connectors » Printed Circuit Board
Body Plating:	Nickel
Connector Body Style:	Right Angle
Contact Plating:	Gold
Frequency Range:	DC - 1 GHz
Gender:	Jack
Impedance:	75 Ohm
Reverse Polarity:	No
RoHS Certificate:	Yes
IGS File Download:	IGS File
More Information:	Customer Drawing Distributor Inventory