







MOD	LOC	DIST	REVISIONS						
27	AD	39	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
						F	REV REDRAWN PER AR2730	10-17-89	—
						G	REV PER ECN AR2785	JPG 11-10-89	—
						H	REV LOC & DIST AD-4171	3-90	BF
						J	REV PER 0010-1410-93	1-8-94	SS
						K	REV PER 0010-1103-93	3-16-94	SAS
						L	REV PER 0010-1175-95	12-30-96	JH
						M	REV PER EC 063C-230-02	23AUL02	DS



SECTION Y-Y 3



SECTION X-X



TYPICAL APPLICATION

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 2 SHEAR LINES DEFINE LOOSE PIECE PART.
- 3 PLAIN.
- 4 .000030 GOLD OVER .000050 NICKEL ENTIRE TERMINAL.
- 5 TIN PLATED.
- 6 GOLD FLASH OVER .000050 NICKEL ENTIRE TERMINAL, .000030 GOLD IN CONTACT AREA ONLY.
- 7 GOLD FLASH OVER .000050 NICKEL ENTIRE TERMINAL, .000015 GOLD IN CONTACT AREA ONLY.
- 8 .000015 GOLD IN CONTACT AREA, .000100-.000200 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
- 9 .000030 GOLD IN CONTACT AREA, .000100-.000200 BRIGHT TIN-LEAD ON TERMINATION AREA, ALL OVER .000050 NICKEL ENTIRE TERMINAL.
- 10 OBSOLETE PART NUMBER.
- 11 .005 SEAM OPENING PERMISSABLE
- 12 NOTED DIMENSIONS CHECKED WITH .000 SEAM OPENING.

9	MINIATURE	85424-7	1-85489-3
8	MINIATURE	85424-6	1-85489-2
7	MINIATURE	85424-5	1-85489-1
6	MINIATURE	85424-4	85489-7
5	MINIATURE	—	85489-6
4	MINIATURE	—	85489-5
6	STANDARD	—	85489-4
5	STANDARD	85424-3	85489-3
4	STANDARD	85424-2	85489-2
3	—	85424-1	85489-1
FINISH	REELED FOR APPLICATOR	LOOSE PIECE PART NO	PART NUMBER

PART NO		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± -		
CHK 10-23-89 SCOTT A SHUEY	AMP INCORPORATED Harrisburg, Pa. 17105	
APPD 10-23-89 MARIAN P CLARK		
APPD 10-23-89 B FLINCHBAUGH		
MATERIAL PHOS. BRONZE	PRODUCT SPEC —	NAME RECEPTACLE, MOD I, STANDARD PRESSURE, TYPE B
FINISH SEE TABLE	APPLICATION SPEC —	
WEIGHT —	—	
SIZE D	CAGE CODE 00779	DRAWING NO 85489
SCALE 10:1	SHEET 1 OF 1	