

High Accuracy Thermo-Hygrometer



Product Description

A high accuracy combined humidity & air temperature meter with wet bulb and dewpoint temperatures. Ideal for a wide range of industrial and laboratory applications. Suitable for single handed operation.

- -30°C to 100°C x 0.1° , 0 to 100%RH x 0.1
- Displays temperature in $^{\circ}\text{C}$ or $^{\circ}\text{F}$
- Dew Point & Wet Bulb temperatures displayed at the touch of a button
- 43mm LCD dual display with backlight
- Connected probe with 1.8m coiled cable
- Probe mounting clip allows single-handed use
- Data Hold freezes displayed measurements
- Min/Max Memory for both temperature and humidity
- Low Battery indication
- Auto Power Off – adjustable from 1 to 120 minutes, can be user disabled
- Impact-resistant ABS case with rubber boot and flip-out desk stand
- Supplied with carry bag & strap, rubber boot and battery

Technical Specification

	Temperature	Humidity	Dewpoint	Wet Bulb
Range	-30° to 100°C	0 to 100% RH	-30° to 100°C	0° to 80°C
Resolution	0.1°C	0.1%RH	0.1°C	
Accuracy	$\pm 1^{\circ}\text{C}$	$\pm 2\%\text{RH}$	$\pm 1.0^{\circ}\text{C}$	
Power	1 x 9V PP3 Alkaline Battery (ALR-61)			
Dimensions	155 x 72 x 35mm			
Weight	210g			

