

PLIERS AND CUTTERS (Cont.)



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5



Fig. 6

Pliers and Cutters

Retail Part No.	Bulk Part No.	Figure No.	Description	Handle Color	Overall Length	Nose Style	Weight (Pounds)
12-300		1	Mini Diagonal Cutting Pliers	Orange	4.00"		0.16
12-306		1	Mini Diagonal Cutting Pliers	Orange	4.50"		0.16
12-312		2	Narrow Diagonal Cutting Pliers	Orange	5.00"		0.22
12-318		3	High Leverage Diagonal Cutting Pliers	Orange	7.00"		0.56
12-500		4	Flush Cutters	Orange	5.00"		
12-504		5	Clip/Grip Flush Cutter	Orange	4.50"		
12-1950		6	Snap Ring Plier Kit	Red	6.50"		



Fig. 7

Precision Electronic Screwdrivers

Retail Part No.	Bulk Part No.	Figure No.	Description	Blade Size	Shaft Diameter	Shaft Length	Handle Length	Overall Length
12-6114		7	Flat Head Screwdriver	1.4 mm	2.0 mm	40 mm	S-80 mm	120 mm
12-6120		7	Flat Head Screwdriver	2.0 mm	2.0 mm	40 mm	S-80 mm	120 mm
12-6220		7	Flat Head Screwdriver	2.0 mm	2.0 mm	75 mm	M-95 mm	170 mm
12-6224		7	Flat Head Screwdriver	2.4 mm	2.4 mm	75 mm	M-95 mm	170 mm
12-6225		7	Flat Head Screwdriver	2.4 mm	2.4 mm	100 mm	M-95 mm	195 mm
12-6231		7	Flat Head Screwdriver	3.0 mm	3.0 mm	150 mm	M-95 mm	245 mm
12-6330		7	Flat Head Screwdriver	3.0 mm	3.0 mm	100 mm	L-105 mm	205 mm
12-6341		7	Flat Head Screwdriver	4.0 mm	4.0 mm	150 mm	L-105 mm	255 mm