


# Speaker Wire

UL Listed or AWM Style 1007



| CATALOG NUMBER | NUMBER OF COND. | AWG SIZE | COND. STRAND | NOM. INSULATION THICKNESS |      | NOMINAL O.D. |           |
|----------------|-----------------|----------|--------------|---------------------------|------|--------------|-----------|
|                |                 |          |              | INCHES                    | mm   | INCHES       | mm        |
| <b>C1356</b>   | 2               | 24       | 7/32         | 0.016                     | 0.41 | 0.058x0.117  | 1.47x2.79 |
| <b>C1362</b>   | 2               | 22       | 7/30         | 0.020                     | 0.51 | 0.070x0.145  | 1.77x3.68 |
| <b>C1360</b>   | 2               | 20       | 10/30        | 0.020                     | 0.51 | 0.085x0.160  | 2.16x4.06 |
| <b>C1357</b>   | 2               | 18       | 16/30        | 0.020                     | 0.51 | 0.083x0.181  | 2.11x4.60 |
| <b>C1358</b>   | 2               | 16       | 26/30        | 0.020                     | 0.51 | 0.105x0.210  | 2.67x5.33 |
| <b>C1361</b>   | 2               | 14       | 41/30        | 0.025                     | 0.64 | 0.125x0.235  | 3.18x5.69 |
| <b>C1363</b>   | 2               | 12       | 65/30        | 0.025                     | 0.64 | 0.154x0.323  | 3.91x8.20 |

## Color Code Chart

| ORDERING SUFFIX | COLORS |
|-----------------|--------|
| <b>01</b>       | Black  |
| <b>02</b>       | White  |
| <b>08</b>       | Brown  |
| <b>10</b>       | Gray   |
| <b>90</b>       | Clear  |

## Product Construction:

### Conductor:

- 24 thru 12 AWG fully annealed one bare, one tin stranded copper per ASTM B-174

### Insulation/Jacket:

- Premium-grade PVC
- Color code: See chart below

## Applications:

- Digital audio
- Hi-fi and stereo speaker wire
- Jukeboxes
- Not for in-wall use
- Home theater

## Compliances:

- UL Wires Misc.
- RoHS Compliant Directive 2002/95/EC

## Packaging:

- Please contact Customer Service for packaging and color options



| CATALOG NUMBER | NO. OF COND. | AWG SIZE | COND. STRAND | NOM. INSULATION THICKNESS |      | NOMINAL O.D. |      |
|----------------|--------------|----------|--------------|---------------------------|------|--------------|------|
|                |              |          |              | INCHES                    | mm   | INCHES       | mm   |
| <b>C7102A</b>  | 2            | 18       | 7/.0152      | 0.020                     | 0.51 | 0.172        | 4.37 |

## Color Code Chart

| ORDERING SUFFIX | STOCK COLOR |
|-----------------|-------------|
| <b>99</b>       | Black-White |

## Product Construction:

### Conductor:

- 18 AWG tinned annealed stranded copper
- Stranded tinned copper per ASTM B-33

### Insulation:

- Premium-grade, color-coded PVC
- Temperature range: -30°C to +80°C
- Color code: See chart below

## Applications:

- Audio systems
- Not for in-wall use

## Compliances:

- UL Style 1007 (UL: 80°C, 900V)

## Packaging:

- 1000' (305m) reels