





PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR MATERIAL: PBT
FLAMMABILITY RATING: UL94-V0
COLOUR: BLACK
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: SELECTIVE GOLD
SHIELDING: BRONZE NI PLATED
QUALITY CLASS: 750 MATING CYCLES

LED COLOR
LED 1: YELLOW
LED 2: GREEN



ENVIRONMENTAL
OPERATING TEMPERATURE: -40 °C UP TO 85 °C
COMPLIANCE: LEAD FREE AND ROHS


ELECTRICAL
CURRENT RATING: 1.5 A
WORKING VOLTAGE: 120 VAC
INSULATION RESISTANCE: >500 MΩ
DIELECTRIC WITHSTANDING VOLTAGE: 1 000 VAC/MIN
CONTACT RESISTANCE: 20 mΩ MAX

STANDARD
 CERTIFIED: E324776

SOLDERING

JEDEC LEAD FREE WAVE SOLDERING PROCESS

PACKAGING
TRAY

RoHS Compliant					GENERAL TOLERANCE $.X = +/_ 0.2$ $.XX = +/_ 0.15$		DESCRIPTION: HORIZONTAL SHIELDED WITH LED AND EMI PANEL FINGER 8P8C MODULAR JACK TAB UP	SIZE A4
G								
F								
E	05-SEP-14	GENERAL UPDATE	AS					
D	03-JAN-14	UL & TEMP UPDATE	QL	APPROVAL: RJ	UNIT: MM	WERI PART NO: 615 008 137 421		
C	20-AUG-13	DIM UPDATE	QL		SCALE:			
B	27-FEB-09	LED COLOUR	JP		SHEET: 1/1			
A	21-NOV-07	PDF	CH		DRAW:			
REV	DATE	FILE	BY					