


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191980047](#)
Status: **Active**
Description: Avikrimp™ Spade Tongue Terminal for 10-12 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Ring and Spade Terminals
Series	19198
Mil-Spec	N/A
Product Name	Avikrimp™
Type	Spade
Physical	
Barrel Type	Closed
Flammability	94V-0
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min: Mating (µin)	100
Plating min: Mating (µm)	2.5
Plating min: Termination (µin)	100
Plating min: Termination (µm)	2.5
Stud Size	8 (M4)
Wire Insulation Diameter	5.70mm (.225") max.
Wire Size AWG	10
Wire Size AWG	12
Wire Size mm²	3.30 - 5.00
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	C-841-08
Reference - Drawing Numbers	
Sales Drawing	CCD80302



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19198 Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Hand Crimp Tool	0640011500
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION