



Wiha. Premium Tools  
for Professionals.

## Wiha PicoFinish. The Specialist for Precision Applications.



*The soft material of the handle, together with the rotating cap, enables optimum and sensitive twisting.*



*The clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver.*




The Wiha PicoFinish screwdrivers are predestined for high-precision work, predominantly with electro-technical and precision components.

The octagonal rapid-rotation zone at the front of the handle allows rapid twisting.

The extraordinarily easy-to-twist rotating cap permits the delicate turning of fine screws with just one hand.

### PicoFinish Advantages:

- Special soft plastic material assures comfortable, delicate work
- Ideal for fine adjustments in electronic assembly work and precision applications, as well as for hobby use and model making
- Clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver
- Convex handle end allows the transmission of a controlled high torque to powerfully tighten or loosen the screw head
- Palm saving rotating cap with a large surface for the fingers makes incremental adjustment easy
- Wiha ChromeTop-finish on tip for a perfect fit every time





Wiha. Premium Tools  
for Professionals.

## Wiha PicoFinish. The Specialist for Precision Applications.

### For Hexagon Socket Screws.



#### 263 P Hex Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

| Order-No. | Hex | Cap | Shank | Tip | Length |
|-----------|-----|-----|-------|-----|--------|
| 00519 1   | 0.7 | 40  | 140   | 18  | 10     |
| 00520 7   | 0.9 | 40  | 140   | 18  | 10     |
| 00521 4   | 1.3 | 40  | 140   | 18  | 10     |
| 00522 1   | 1.5 | 50  | 150   | 18  | 10     |
| 00523 8   | 2   | 50  | 150   | 18  | 10     |
| 00524 5   | 2.5 | 60  | 160   | 18  | 10     |
| 00525 2   | 3   | 60  | 160   | 18  | 10     |

#### 263 P Inch Hex Screwdriver.

With rotating cap and rapid-turning zone. Inch sizes.

| Order-No. | Hex    | Cap | Shank | Tip | Length |
|-----------|--------|-----|-------|-----|--------|
| 00519 1   | 0.028" | 40  | 140   | 18  | 10     |
| 00520 7   | 0.035" | 40  | 140   | 18  | 10     |
| 00521 4   | 0.050" | 40  | 140   | 18  | 10     |
| 00526 9   | 1/16"  | 50  | 150   | 18  | 10     |
| 00523 8   | 5/64"  | 50  | 150   | 18  | 10     |
| 00528 3   | 3/32"  | 60  | 150   | 18  | 10     |
| 00530 6   | 7/64"  | 60  | 150   | 18  | 10     |
| 00527 6   | 1/8"   | 60  | 150   | 18  | 10     |

### For Hexagon Socket Screws.



#### 264 P Ballpoint Hex Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Extra: Ballpoint allows up to 25 degree entry angle to fastener.

| Order-No. | Hex | Cap | Shank | Tip | Length |
|-----------|-----|-----|-------|-----|--------|
| 00531 3   | 1.3 | 40  | 140   | 18  | 10     |
| 00532 0   | 1.5 | 50  | 150   | 18  | 10     |
| 00533 7   | 2   | 50  | 150   | 18  | 10     |
| 00534 4   | 2.5 | 60  | 160   | 18  | 10     |
| 00535 1   | 3   | 60  | 160   | 18  | 10     |

#### 264 P Inch Ballpoint Hex Screwdriver.

With rotating cap and rapid-turning zone. Inch sizes.

| Order-No. | Hex    | Cap | Shank | Tip | Length |
|-----------|--------|-----|-------|-----|--------|
| 00531 5   | 0.050" | 40  | 120   | 18  | 10     |
| 00537 5   | 1/16"  | 50  | 150   | 18  | 10     |
| 00541 2   | 5/64"  | 50  | 150   | 18  | 10     |
| 00539 9   | 3/32"  | 50  | 150   | 18  | 10     |
| 00542 9   | 7/64"  | 60  | 160   | 18  | 10     |
| 00538 2   | 1/8"   | 60  | 160   | 18  | 10     |
| 00543 6   | 9/64"  | 60  | 160   | 18  | 10     |
| 00540 5   | 5/32"  | 60  | 160   | 18  | 10     |