



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

RoHS Compliant

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
B	ECN 4859: REVISED SERIES MICRO B MOLDED HOOD	6/23/10	D.FRISIELLO
C	ECN 5868: ADDED LENGTHS 03 M, 075 M, REVISED WIRE MAP	12/7/11	D.FRISIELLO
D	ECN5915: REVISED VIEWS OF USB MICRO B MALE	01/10/12	DFP
E	ECN6237: ADDED CONTACT PLATING NOTE. UPDATED FORMAT.	09/17/12	DFP



MODEL NUMBER	LENGTH METERS [FEET]
CSMUAMICB-03M	0.3 [.98]
CSMUAMICB-05M	0.5 [1.64]
CSMUAMICB-075M	0.75 [2.46]
CSMUAMICB-1M	1.0 [3.28]
CSMUAMICB-2M	2.0 [6.56]
CSMUAMICB-3M	3.0 [9.84]



NOTES:

1. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION.
2. CABLE ASSEMBLY SHALL MEET USB 2.0 REQUIREMENTS.
3. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: 012 [305] = +1 [25] / -0 >12 [305] 060 [1524] = +2 [51] / -0 >60 [1524] 0120 [3048] = +4 [102] / -0 >120 [3048] 0300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = 0.2 .XX = 0.02 .XXX = 0.005	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	06/03/2010		
	CHECKED BY D. CASTRO	06/03/2010	CATEGORY USB	
	APPROVED BY S. SMITH	06/03/2010	PRODUCT DESCRIPTION CBL, USB-A/MICRO B	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. CSMUAMICB	REV. E	SCALE: NONE
		CAD FILE: CSMUAMICB.SLDDRW	SHEET 1 OF 1	