

# 4600 and 4400 series

## Toggle switches

*Distinctive features and specifications*

UG1006-A



- ☐ High current/voltage rating in a small case
- ☐ Butt action contacts
- ☐ Insulated or metal lever
- ☐ UL, CSA and VDE (EN 61058-1) approved

### ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
  - silver contacts (A) : 4A 250VAC - 6A 125VAC
  - silver plated copper contacts (C) : 2A 250VAC - 3A 125VAC
- Approved electrical ratings : see table below
- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
  - 2.000 Vrms 50 Hz min. between terminals
  - 2.500 Vrms 50 Hz min. between poles and between terminals and frame
- Electrical life : 10.000 cycles at full load

| APPROVALS           | MODELS | POLES | FUNCTIONS | APPROVED RATINGS      |
|---------------------|--------|-------|-----------|-----------------------|
| UL/CSA              | 4600A  | 1-2   | 1-6-9     | 3A 250VAC - 6A 125VAC |
| VDE<br>(EN 61058-1) | 4400A  | 1-2   | 1-6       | 4(2)A 250VAC          |
|                     | 4600A  | 1-2-3 | 1-6       | 4(2)A 250VAC          |

### MATERIALS

- Case : melamine phenolic
- Actuator :
  - insulated : polyamide ,6-6
  - non-insulated : brass, nickel plated
- Bushing :
  - insulated : polyamide 6-6
  - non-insulated : brass, nickel plated
- Contacts :
  - A : silver
  - C : copper, silver plated

### GENERAL SPECIFICATIONS

- Torque : 0,95 Nm (.70 Ft.lb) max. applied to nut
- Panel thickness : 5 mm (.196) between 2 nuts
- Operating temperature : -20°C to +55°C
- Hand soldering : 270°C max. for 10 seconds max. - iron Ø3 (.118)

### AGENCY APPROVALS



EN 61058-1

**Availability** : see above chart.



**Marking** : VDE approved models are standard marked.

To order switches marked UL-CSA, complete appropriate box of ordering format.

# 4600 and 4400 series

## Toggle switches

### Overview



### ABOUT THIS SERIES

**Dimensions** : first dimensions are in mm while inches are shown as bracketted numbers.



**NOTICE** : please note that not all combinations of above numbers are available. Refer to the following pages for further information.



**Sealing boots** are available on 3 pole models to protect the switches against dust and water. They are presented in section H.



**Mounting accessories** : standard hardware supplied with all models : 1 hex nut U166 and 1 knurled nut U520 in the same colour as the lever (insulated models) or U411 nickel plated (metal lever models). Standard and special hardware available are presented in section I.



**Packaging unit** : 20 pieces.


# 4600 and 4400 series

## Toggle switches



Insulated flat lever

MODEL  
STRUCTURE

→ Keyway



- Solder lug/quick-connect terminals 2,8 x 0,5 (.110 x .019)
- Straight PC terminals or quick-connect terminals 4,7 x 0,8 (.185 x .031)
- 2 and 3 maintained positions
- 1 and 2 pole configurations



MODEL  
STRUCTURE





### Solder lug/quick-connect terminals - single pole

→ Keyway



4631 -2  
4636 -2  
4639 -2

| III | II  | I   |
|-----|-----|-----|
| ON  | -   | OFF |
| ON  | -   | ON  |
| ON  | OFF | ON  |





### Solder lug/quick-connect terminals - double pole

→ Keyway



4641 -2  
4646 -2  
4649 -2

| III | II  | I   |
|-----|-----|-----|
| ON  | -   | OFF |
| ON  | -   | ON  |
| ON  | OFF | ON  |





### Straight PC terminals - single pole

→ Keyway



4431 -2  
4436 -2  
4439 -2

| III | II  | I   |
|-----|-----|-----|
| ON  | -   | OFF |
| ON  | -   | ON  |
| ON  | OFF | ON  |



# 4600 and 4400 series

Toggle switches

Insulated flat lever



## Straight PC terminals - double pole



4441 -2  
4446 -2  
4449 -2

| III | II  | I   |
|-----|-----|-----|
| ON  | -   | OFF |
| ON  | -   | ON  |
| ON  | OFF | ON  |

→ Keyway





## Quick-connect terminals 4,7 x 0,8 (.185 x .031) - single pole




4631/8 -2  
4636/8 -2

| I  |   | II  |
|----|---|-----|
| ON | - | OFF |
| ON | - | ON  |

→ Keyway



## PANEL CUT-OUT




# 4600 and 4400 series

## Toggle switches



Round lever - three pole

MODEL  
STRUCTURE

→ Keyway



- Solder lug or straight PC terminals
- 2 and 3 maintained positions



MODEL  
STRUCTURE





### Solder lug terminals - metal lever

→ Keyway



4651  
4656  
4659

| III | II  | I   |
|-----|-----|-----|
| ON  | -   | OFF |
| ON  | -   | ON  |
| ON  | OFF | ON  |





### Straight PC terminals - metal lever

→ Keyway



4451  
4456  
4459

| III | II  | I   |
|-----|-----|-----|
| ON  | -   | OFF |
| ON  | -   | ON  |
| ON  | OFF | ON  |





### Solder lug terminals - insulated lever - silver contacts

→ Keyway



4651A-32  
4656A-32

| I  | II  |
|----|-----|
| ON | -   |
| ON | -   |
| ON | OFF |
| ON | ON  |






# 4600 and 4400 series


Toggle switches

## CONTACT MATERIALS




- A** Silver  
**C** Copper, silver plated

## ACTUATORS



- Blank** Round, metal lever for 3 pole only  
**-2** Insulated flat lever (for single and double pole only)  
**-32** Black insulated round lever (for 3 pole only)

## ACTUATOR COLOURS




- 1** Blue  
**2** Black (standard)  
**3** Green  
**4** Grey  
**5** Yellow  
**6** Red  
**7/1** White  
**9** Orange



For insulated flat lever  
Black : standard colour - reduced delivery time  
Minimum order of 500 pieces for non-standard colours.

## APPROVALS



**UU (UL-CSA)** Single and double pole only

**Availability** : see specifications for details of approved models.

**Marking** : to order switches marked UL-CSA, complete above box with 'UU'.  
Other approvals available as standard, see specifications.