




Micro Commercial Components

Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

DB3/DC34 AND DB4/DB6

SILICON BIDIRECTIONAL DIAC

DO-35G



Features

- The three layer, two terminal, axial lead, hermetically sealed diacs are designed specifically for triggering thyristors.
- Lead Free Finish/Rohs Compliant (Note1) ("P" Suffix designates Compliant. See ordering information)
- Moisture Sensitivity: Level 1 per J-STD-020C
- These diacs are intended for use in thyristors phase control , circuits for lamp dimming, universal motor speed control ,and heat control. Type number is marked.

Maximum Ratings

- Operating Temperature: -40°C to +110°C
- Storage Temperature: -40°C to +125°C

Electrical Characteristics @ 25°C Unless Otherwise Specified

Power dissipation on Printed Circuit(l=10mm)	P_C	150mW	$T_A=50^{\circ}\text{C}$
Repetitive Peak on-state Current DB3,DC34,DB4 DB6	I_{TRM}	2.0A 16A	$t_p=10\mu\text{s}, f=100\text{Hz}$
Breakover Voltage DB3 DC34 DB4 DB6	V_{BO}	Min Typ Max 28 32 36V 30 34 38V 35 40 45V 56 60 70V	$C=22\text{nF}(\text{Note } 3)$
Breakover Voltage Symmetry DB3, DC34, DB4 DB6	$ +V_{BO} $ $ -V_{BO} $	$\pm 3\text{V}$ $\pm 4\text{V}$	$C=22\text{nF}(\text{Note } 3)$
Output Voltage(Note 2)	$V_{o(\min)}$	5V	
Breakover Current(Note 2)	$I_{BO(\max)}$	100uA	$C=22\text{nF}$
Rise Time(Note 2)	T_r	1.5us	
Leakage Current(Note 2)	$I_{B(\max)}$	10uA	$V_B=0.5V_{BO(\max)}$

- Note: 1. Lead in Glass Exemption Applied, see EU Directive Annex 5.
2. Electrical characteristics applicable in both forward and reverse directions.
3. Connected in parallel with the devices.

DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	---	.150	---	3.8	
B	---	.079	---	2.00	
C	---	.020	---	.52	
D	1.083	---	27.50	---	

RATINGS AND CHARACTERISTIC CURVES DB3/DC34/DB4/DB6

DIAGRAM 1: Current-voltage characteristics




DIAGRAM 2: Test circuit for output voltage




DIAGRAM 3: Test circuit see diagram2 adjust R for $I=0.5A$




FIG.1-Power dissipation versus ambient temperature (maximum values)




FIG.3-Peak pulse current versus pulse duration (maximum values)





FIG.2-Relative variation of VBO versus junction temperature (typical values)



Ordering Information

Device	Packing
(Part Number)-TP	Tape&Reel; 10Kpcs/Reel
(Part Number)-AP	Ammo Packing;5Kpcs/AmmoBox
(Part Number)-BP	Bulk;500pcs/Bag

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . *Micro Commercial Components Corp.* does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp.* and all the companies whose products are represented on our website, harmless against all damages.

APPLICATIONS DISCLAIMER

Products offer by *Micro Commercial Components Corp.* are not intended for use in Medical, Aerospace or Military Applications.