

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020252](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Switch

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
UL E59251

General

Product Family Portable Lighting
Series [130102](#)
NEMA Configuration N/A
Outlet None
Overview [Hand Lamps](#)
Product Name Safety Yellow
Type Hand Lamps
UPC 78678860131

Physical

Cord Length - Primary N/A
Cord Length - Secondary N/A
Depth 101.60mm (4.000")
Duty Commercial
Guard Included Yes
Guard Type Reflector, Screw Release
Height 381.00mm (15.000")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch Yes
Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 271S



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130102](#) Series