

Corded UPS Backplate Outlet Kit - Adds AC plug-in connection and AC output receptacles to SU6000RT3U and SU6000RT3UXR UPS for use with 208V UPS output voltage configurations

MODEL NUMBER: **SUPDM12**



Highlights

- Converts Tripp Lite's hardwire SU6000RT3U UPS systems to one with AC plug and outlets
- For use with 208V mains and UPS output voltage configurations
- 10 ft. / 3m AC input power cable with NEMA L6-30P input plug
- 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Applications

- Ideal for 208V applications calling for Tripp Lite's SU6000RT3U and SU6000RT3UXR UPS systems where plug-in AC input and output connections are required

Description

Tripp Lite's SUPDM12 corded backplate kit converts Tripp Lite's hardwire SU6000RT3U or SU6000RT3UXR UPS system into one with AC plug and outlets. 10 ft./3m input line cord with L6-30P plug enables simple connection to 208V 30A mains power. Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles. Easy quick-connect wiring installs in minutes.

VOLTAGE COMPATIBILITY NOTE - SUPDM12 supports SU6000RT3U and SU6000RT3UXR applications configured for 208V nominal input voltage only (See SUPDM13 for 240V input voltage configurations).

Features

- Converts Tripp Lite's hardwire SU6000RT3U or SU6000RT3UXR UPS system to one with an AC plug and outlets
- 10 ft./3m AC line cord with L6-30P input plug-in connection
- Includes 1 L6-30R, 2 L6-20R and 10 5-15/20R output receptacles
- Easy quick-connect wiring installs in minutes

Specifications

OVERVIEW	
Model Type	Outlet Kits
OUTPUT	
Output Nominal Voltage	Simultaneous 208 and 120V output
Overload Protection	120V outlets are protected by 2 separate 20A branch rated circuit breakers



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Outlet Quantity / Type	208V: 1 L6-30R, 2 L6-20R / 120V: 10 5-15/20R
Number of Outlets	13
INPUT	
Nominal Input Voltage(s) Supported	208V AC
UPS Input Cord Length (ft.)	10 ft. / 3m
UPS Input Cord Length (m)	3.05
Recommended Electrical Service	30A 208V
Input Connection Type	NEMA L6-30P input plug
Voltage Compatibility (VAC)	208
PHYSICAL	
Shipping Dimensions (hwd / in.)	5.5 x 9 x 14.25
Shipping Dimensions (hwd / cm)	14 x 22.9 x 36.2
Shipping Weight (lbs.)	6.6
Shipping Weight (kg)	3
Unit Dimensions (hwd / in.)	2.5 x 5 x 11
Unit Dimensions (hwd / cm)	6.4 x 12.7 x 28
Unit Weight (lbs.)	6
Unit Weight (kg)	2.8
Material of Construction	Steel
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.