

You are here: [Products](#) » [Connectors f.con](#) » [PCB connectors](#) » [Male headers](#) » [SL 2 ... / SL 22 ...](#) » [SL 22 190](#)



► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

▼ PCB connectors

■ [Male headers](#)

■ Female headers

■ Direct female connector

■ Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

Male headers

SL 22 190 12 G

square 0.635 mm, standard

add to request



Features

Technical Drawing

Variants

no. of contacts	12
contact material	CuSn-Legierung
surface contact /	Ni+0,2µm Au
contact sleeve	Ni+4...6µm Sn
surface of contact	gold-plated
volume resistivity	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
material isolation body	PA 4.6, GF
temperature range	-40 °C ... +163 °C (260 °C / 10 s)
class of flammability	UL 94 V-0
insulation resistance	>10 ¹² Ω
connection type	soldering
version	standard
reflow solderable	yes