




# Top Willing Co., Ltd.

| 編號<br>ITEM NO.    | 圖號<br>DRAWING NO. | 版次<br>EDITION | A 版            |
|-------------------|-------------------|---------------|----------------|
| 電鍍<br>PLATING     | 日期<br>DATE        | 製圖<br>DRAWER  | Elva           |
| 描述<br>DESCRIPTION | 單位<br>UNIT        | 比例<br>SCALE   | 5.1:1          |
|                   | 公差<br>TOLERANCE   | 設計<br>DESIGN  | 核定<br>APPROVED |
|                   |                   |               |                |

RB-322-ROHS

NGD

RCA JACK TO  
BNC JACK ADAPTER

.\\R\RB-322-ROHS

2006 年 03 月 02 日

mm

0-0.5mm ± 0.10mm  
0.5-8mm ± 0.20mm  
8-30mm ± 0.40mm  
30-120mm ± 0.50mm

| NO | DESCRIPTION  | Q'TY | ITEM NO.    | MATERIAL | PLATING |
|----|--------------|------|-------------|----------|---------|
| 1  | BODY 1       | 1    | RB-322-ROHS | BRASS    | NICKEL  |
| 2  | BODY 2       | 1    | B-211-ROHS  | BRASS    | NICKEL  |
| 3  | DIELECTRIC 1 | 1    | D-060012    | DELRIN   | -       |
| 4  | DIELECTRIC 2 | 1    | D-060016    | DELRIN   | -       |
| 5  | CENTER PIN   | 1    | RB-322-ROHS | BRASS    | GOLD    |

NGD: 1<sup>st</sup> N is Nickel for body. 2<sup>nd</sup> G is Gold for pin.  
3<sup>rd</sup> D is Delrin for insulation.