




HEYClip™ “P” Style Wire and Cable Holder

MAXIMUM BUNDLE DIAMETER		PART NO. Natural	DESCRIPTION	FOOTPRINT A x B		OVERALL HEIGHT C		MOUNTING HOLE DIA.	
in.	mm.			in.	mm.	in.	mm.	in.	mm.
.620	15,7	3598	CH RJ-625	.22 x 1.00	5,6 x 25,4	1.70	42,9	.19	4,8

For Panels .09” (2,3 mm) Thick*
Standard color natural.
*.31” (7,8 mm) bayonet length.

- Push mount design for fast installation.
- Maximum panel thickness is .090” (2,3 mm).
- Mounting hole diameter is .187” (4,8 mm).
- Footprint x Overall Height (A x B x C) = maximum rectangular prism occupied by part.



“P” Style Wire and Cable Holder

Standard Lockit Loop

Push Mount Lockit Loop

HEYClip™ Lockit™ Loops

More Positive Lock!

MAXIMUM BUNDLE DIAMETER		PART NO. Natural	DESCRIPTION	OVERALL HEIGHT C		MOUNTING HOLE DIAMETER	
in.	mm.			in.	mm.	in.	mm.
Standard Loops							
.250	6,4	3793	LL 250	.84	21,2		
.375	9,5	3795	LL 375	1.02	25,9	n/a	n/a
.500	12,7	3797	LL 500	1.20	30,4		
.750	19,1	3799	LL 750	1.45	36,8		
Push Mount Loop							
.250	6,4	3778	PMLL 250	.79	20,1		
.375	9,5	3779	PMLL 375	.98	24,9	.19	4,7
.500	12,7	3780	PMLL 500	1.12	28,5		
.750	19,1	3782	PMLL 750	1.41	35,8		
1.000	25,4	3796	PMLL 1000*	2.14	53,9	.25	6,4

Standard color natural.
*For Panels up to .06” (1,5 mm) Thick. Bayonet length is .39” (10,0 mm).

- Barreled ends for greater holding power.
- Smooth, rounded edges ensure that Lockit Clips won’t cut into cable’s insulation—or the installer’s hand.
- Releasable and reusable loops for easy wire bundling.
- Locking ends “twist” into place with fingertip pressure.

Material	Nylon 6/6
Flammability Rating	94V-2

Quick Specs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3860](#) [3780](#) [3796](#) [3782](#) [3795](#) [3793](#) [3797](#) [3779](#) [3598](#) [3778](#)