

Search Product:

Submit

[[Advanced](#)]

- ? [Adapters & power supplies](#)
- ? [Batteries & chargers](#)
- ? [Cables & accessories](#)
- ? [Connectors](#)
- ? [Consumer products & pc acc.](#)
- ? [Electronic components](#)
- ? [High-q tools & dmm's](#)
- ? [Led products & lamps](#)
- ? [Light products](#)
- ? [Loudspeakers & pa systems](#)
- ? [Perel tools](#)
- ? [Security products](#)
- ? [Velleman kits & oscilloscopes](#)

[ROHS Info](#)

[HIGH -Q TOOLS & DMM'S](#) > [MULTIMETERS](#) > [DIGITAL MULTIMETERS](#) >



3 1/2 DMM - 10A / HOLD FUNCTION / BACKLIGHT

Order Code: DVM850BL



Features

- ? DMM with automatic polarity function and 3 ½ digit LCD display
- ? measurements: DC current up to 10A, AC and DC voltage up to 600V, resistance up to 2Mohm
- ? diode, transistor and continuity test with buzzer
- ? data-hold function and backlight
- ? with protection holster

Specifications

- ? DC voltage: 200m/2/20/200/1000V
 - ? basic accuracy: -
 - ? input impedance: -
 - ? maximum input: 600V
- ? AC voltage: 200/600
 - ? basic accuracy: -
 - ? input impedance: -
 - ? frequency range: -
 - ? maximum input: 600V
- ? DC current: 200µ /2m/20m/200m/10A
 - ? basic accuracy: -
 - ? overload protection: 10A
- ? AC current: -
 - ? basic accuracy: -
 - ? overload protection: -
- ? resistance: 200/2k/20k/200k/2M
 - ? basic accuracy: -
 - ? overload protection: -
- ? capacitance: -
 - ? accuracy: -
- ? inductance: -
 - ? accuracy: -
- ? frequency: -
 - ? basic accuracy: -
 - ? overload protection: -
- ? temperature: -
 - ? basic accuracy: -
- ? overrange: yes "1"
- ? continuity buzzer: yes
- ? transistor test: yes
- ? diode test: yes
- ? low-battery indication: -
- ? maximum display: 1999
- ? LCD display size: 1.8" x 0.7"
- ? ranging mode: manual
- ? data hold: yes
- ? backlight: yes
- ? dimensions: 2.7" x 5.4" x 1.2"
- ? weight (with battery): 13.2275 oz
- ? power supply: 1 9V 6LR61 battery (incl.)
- ? packing: -
- ? accessories:-
- ? auto power-off: no

Files

- ? [EN- FR- NL- ES- DE- PL](#)

Stock Info

- ? Inner carton: 10
- ? Outer Carton: 40
- ? EAN Barcode: 5410329204648
- ? Packaging: Double Blister