

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191930289

Status:

Active - Custom

Description:

VersaKrimp™ Ring Tongue Terminal for 4 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E32244

General

Product Family

Series

Crimp Quality Equipment

Mil-Spec

Product Name

Type

Ring and Spade Terminals

19193

Yes

N/A

VersaKrimp™

Ring

Physical

Barrel Type

Insulation

Material - Plating Mating

Packaging Type

Plating min - Mating

Plating min - Termination

Stud Size

Termination Interface: Style

Wire Size AWG

Closed - Brazed

None

Tin

Bag

2.540µm (100µ")

2.540µm (100µ")

3/4" (M18)

Crimp or Compression

4

Material Info

Old Part Number

F-370-34

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-013

SD-19193-006



image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19193Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008
Manual Putt Pump Hydraulic System, Die set required	0192860117
Die Set (large) for the HHLS Hydralic Crimper	0192900007
Putt Pump Dieless Head System	0192860065
Hand Crimp Tool	0640013900

This document was generated on 03/02/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION