




60 Watt Universal 2-Wire Input Adapter PSAC60W Power Adapter Meets Level VI Efficiency Requirements



Features

- Low Cost
- Efficiency Level VI Compliance
- Class B EMI
- Ecodesign ErP Directive 2009/125/EC Compliant
- Non-vented/Spill-proof Case
- No Load Power consumption <0.5W
- Low Profile Design
- EISA Compliant

Applications

- Portable Equipment
- Peripherals
- Networking
- Gaming Machines

Safety Approvals

- cUL/UL
- CE

Mechanical Characteristics

- Length: 130mm (5.12in)
- Width: 60mm (2.36in)
- Height: 32mm (1.30in)
- Weight: 305g (10.76oz)

Output Specifications

Model	DC Output Voltage	Load		Ripple ⁽¹⁾ P-P (max.)	Regulation Line & Load	Efficiency Level
		Min.	Max.			
PSAC60W-120	+12V	0A	5.0A	200mV	±5%	VI
PSAC60W-180	+18V	0A	3.33A	180mV	±5%	VI
PSAC60W-240	+24V	0A	2.5A	350mV	±5%	VI
PSAC60W-480	+48V	0A	1.25A	480mV	±5%	VI
PSAC60W-560	+56V	0A	1.08A	560mV	±5%	VI

(1) Measured with a 10uF capacitor and a 0.1uF capacitor at output connector terminal and oscilloscope set at 20MHz.

Phihong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at www.phihong.com for the most up-to-date specifications and contact information.

