



Representative

Catalog Number: FO200-50-9
Product ID: 7TAG009630R0030
UPC Number: 78621071242
EAN Number: 05414363021445
Status: A

FO Slotted Loop Tie, White Polyamide (Nylon 6.6) on Hook Side and Low Density Polyethylene on Loop Side for Temperatures up to 104.4 Degrees Celsius (220 F), Length of 228.6mm (9.0 Inches), Width of 19.05mm (0.75 Inches), Thickness of 1.588mm (0.0625 Inches), Tensile Strength Rating of 222.5 Newtons (50 Pounds)

- Enables quick and convenient bundling of data and fiber optic cables.
- Screw and adhesive mounting bases provide multiple mounting options.
- Wrap pre-determined bundle diameters using the convenient slotted head.

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5047 Velcro Ties
Type	Hook and Loop
Special Features	Enables quick and convenient bundling of data and fiber optic cables.
Width	0.75 in ; 19.05 mm
Length	9 in ; 228.6 mm
Bundle Diameter	Max 2 in ; Max 50.8 mm
Material	Nylon/Polyamide
Color	White
Lock Mechanism	Velcro Fastener
Tensile Strength	50 pounds ; 220 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	19.05mm
Length belt/tape/tie	228.6mm
Tie thickness	1.588mm
Min. holding force	222.5N
Band closure	Velcro fastener
Material	Plastic
Material quality	Polyamide/polyethylene PA/PE
Surface protection	Untreated
Halogen free	Y
Colour	White
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N

Packaging

Inner Quantity	10
Outer Quantity	100
Outer Dimensions (inches)	12.5x12.5x23.37
Weight Uom	8.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000067
Catalog Page	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com