


SPC
TECHNOLOGY

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. SPC-F001.DWG

REVISIONS		DOC. NO. SPC-F001 * Effective 7/8/02 * DCP No. 1508							
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRV'D	DATE
1818	A	RELEASED		HO	8/2/04	JN	04/03/08	JN	04/03/08



NOTE: MOULDED PLASTIC COVER NOT SHOWN

SPECIFICATIONS:

- CONNECTOR: 8 POSITION / 4 CONDUCTOR
- LEADWIRE: 26 AWG, 7 STRAND
- LEADWIRE COLORS: BLACK, RED, GREEN, YELLOW
- SPRING WIRE: 0.45mm (0.018 in) DIAMETER, PHOSPHOROUS BRONZE ALLOY
- HOUSING MATERIAL: ABS AND POLYCARBONATE
- COLOR: WHITE
- INSULATION RESISTANCE: $2000\text{M}\Omega$ @ 500 VAC RMS, 60 Hz
- DIELECTRIC STRENGTH: 500 VAC RMS, 60 Hz
- CONTACT RESISTANCE: $20\text{m}\Omega$ @ 15 MILLIOHMS
- CURRENT RATING: 1-1/2 AMPS
- RETENTION FORCE: 76 N (17 lbs)
- CRIMPING STRENGTH: 2.0 Kg (4.4 lbs)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE OUR
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE:	ELECTRONIC FILE				REV
HISHAM ODUH	9/2/04	Modular Jack, Flush Wall Type, Single, RJ11, Quick Mount	SIZE	DMG. NO.	8588-0089	52N9446.DWG	A
CHECKED BY:	DATE:						
Jason Nash	04/03/08						
APPROVED BY:	DATE:		SCALE:	NTS	U.O.M.:	Millimeters	SHEET:
Jason Nash	04/03/08						1 OF 1