

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301050042](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Watertite Wet Location Incandescent Hand Lamp, 100W with LOVOLT In-line Transformer TEFLON Globe with Screw Release TEFLON Guard, Cord Type 14/2 SOOW, 7.62m (50.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130105](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Specialty Lighting](#)
Product Name Watertite
Type Hand Lamps, Specialty Light
UPC 78678862532

Physical

Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary 15.24m (50.0')
Depth 120.65mm (4.750")
Duty Wet Location
Guard Included Yes
Guard Type Screw Release
Height 457.20mm (18.000")
Length N/A
Material - Globe Teflon*
Material - Guard N/A
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Cord Type - Secondary 14/2 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ
Voltage (Secondary) - Maximum 12V AC

Material Info

Engineering Number 1625-12B



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130105](#) Series