

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0755810001

Status:

Active

Overview:

ipass

Description:

0.80mm Pitch, iPass™ Stacked I/O, External Application, Integrated Cage and Connector Assembly, Right Angle, Press-Fit, 136 Circuit, 0.38µm Gold (Au) Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-75586-001 (PDF)

RoHS Certificate of Compliance (PDF)


General	
Product Family	I/O Connectors
Series	75581
Application	Wire-to-Board
Component Type	I/O Plug Connector Subassembly, Receptacle
Overview	ipass
Product Name	iPass™, PCI Express*
Type	N/A

Physical	
Circuits (Loaded)	136
Circuits (maximum)	136
Color - Resin	Black
Durability (mating cycles max)	250
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	1
Orientation	Right Angle
PC Tail Length	2.08mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.80mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.381µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

Electrical	
Current - Maximum per Contact	0.5A
Grounding to Panel	N/A
Shielded	Yes
Voltage - Maximum	30V AC (RMS)/DC

Material Info

Reference - Drawing Numbers



EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Pb

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
75581Series

Mates With
74547 iPass™ Cable Assembly

Use With
75586 Receptacle

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Press-In Tool for iPass™ 16X PCIE	0622030400
iPass™ 16X PCIE Removal Tool	0622030410

This document was generated on 02/08/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75581-0001](#)