

Material and Finish


Body: PBT Thermoplastic
UL94V-0 rated, Color Black

Cover: PBT Thermoplastic
UL94V-0 rated, Color Black



Bushing: Brass, Nickel Plated

Terminals and Contacts:
Phosphor Bronze
Silver Plated

Coil Springs: Spring Steel



M6 Knurled Nut Included
(not installed)



Recommended PCB Layout
(Bottom View)

Electrical Characteristics

Insulation Resistance: 50 Megohms
min. at 100V DC

Contact Resistance:
30 milliohms Max.

Dielectric Strength: 500V AC RMS
for one minute

Temperature Rating:
Operating Temp: -25°C to +80°C

Mechanical Characteristics

Insertion Force: 0.3kg - 3.0kg

Extraction Force: 0.3kg - 3.0kg

Durability: 5000 Mating Cycles

Tolerances	
X.X	± 0.25
X.XX	± 0.15
Unless Stated Otherwise	

RoHS COMPLIANT
EU Directive 2002/95/EC



STX-3150-3CM

3.5mm Mono Jack, 3Pos., RoHS Compliant

Threaded, Slim Design With Switch

KYCON

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE	UNITS
A0	9/28/05	New Drawing	R. Aguirre	H. MA	R. Aguirre	07/14/05	mm
A1	6/5/06	Release Drawing		H. MA			
B1	07/24/09	ECO #09-047	S. Vien	H. MA			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[STX-3150-3CM](#)