



Red Hybrid Displays

Device Type	Luminous Intensity per Segment or per Diode		typ	@	IF	Key Features
	typ	@	IF	typ	@	
	μcd		mA	V	mA	
TIL302	275	20	3.4	20		0.27 inch high numeric display with decimal point in 14-lead dual-in-line plastic package Same as TIL302 except right hand decimal point Polarity and overflow unit 0.3 inch high alpha-numeric character display in 5 x 7 dot matrix. 14-pin dual-in-line package
TIL303	275	20	3.4	20		
TIL304	275	20	3.4	20		
TIL305	110	10	1.65	10		
TIL306*	275	*	*	*	*	
TIL307*	275	*	*	*	*	0.27 inch high numeric display with logic in 16-pin dual-in-line package. Logic includes decade counter, latch, current source driver, and decoder Same as TIL306 except right hand decimal point Same as TIL306 except logic chip does not include decade counter. Same as TIL308 except right hand decimal point
TIL308*	275	*	*	*	*	
TIL309*	275	*	*	*	*	
TIL311*	110	*	*	*	*	


* Contains Integral Logic NOTE: Hermetic versions available Details on request.




TIL311




TIL302 (TIL303)




TIL304



TIL305



TIL306, 308 (TIL307, 309)



TIL311—Resultant display of binary data