



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click to remove) [Search Tips](#) ☐ Within Results

Text Search: 'STP6X45BU'

Your search criteria matched only one product, shown below

STP6X45BU



- Exceed draft requirements of TIA/EIA-568-B.2-AD10 and ISO 11801 Class E_A Edition 2.1 and IEEE 802.3an-2006 ratified standard channel requirements for supporting 10GBASE-T
- Each patch cord is 100% performance tested and wired T568B
- Constructed of 26 AWG stranded shielded copper cable (nominal cable diameter is .23 inches) and TX6™ Shielded Modular Plugs for superior performance
- Cable has overall metal shield that provides conductive path for grounding
- Plug meets all applicable FCC part 68 Subpart F requirements and exceeds IEC 60603-7 specifications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Plug performance in center of TIA/EIA component range, ensuring interoperability and 10GBASE-T Ethernet channel performance
- Labels on patch cords provide identification of performance level, length, and quality control number

- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes

Part Number	STP6X45BU
RoHS Compliancy Status	Compliant
Part Description	Category 6A, 10 Gb/s STP patch cord w ith TX6™ PLUS Modular Plugs on each end.
Product Type	Copper Patch Cord
Color	Blue
Length (ft.)	45
Length (m)	13.72
Boot Color	Black
Cable Color	Blue
Cable Type	STP
Flammability Rating	CM
Performance Level	Category 6A
Pricing Description	Copper Patch Cord, Category 6A, Blue STP Cable, 45 Feet
Wiring Scheme	T568B
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.