

1001

FILE NO.

C-CD-201-02


- ① MAT'L: COPPER (STOCK THK. $\frac{.040}{1.02}$)
PLATING: ELECTRO-TIN (.0003 MIN.)
② INSULATION: MOLDED PVC (YELLOW)

STUD SIZES: ($\alpha=0.005$)

02 = .094
04 = .119
06 = .146
08 = .173
10 = .198
14 = .265
56 = .328
38 = .390

"UL" LISTING #E32244
"CSA" LISTING #18689

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$



MWID = MAXIMUM WIRE
 INSULATION DIAMETER
 WIRE SIZE: 12-10 AWG
 4.0-6.0MM²

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19179-0019](#) [19179-0014](#)