

4000-7000 BTU/H Indoor Air Conditioner *DTS Series*

Type 12, Side Mounting



Description

- Designed for side mounting on any enclosure surface where high capacity system cooling is required.
- Closed loop cooling ensures clean enclosure air is recirculated without ever mixing with contaminated ambient air.
- Optimum air circulation with maximum clearance distance between warm inlet and cold outlet for reduced hot spot locations.

Standards

- Maintains enclosure's NEMA 12 rating
- IP 54
- UL, cUL and CE


Features

- R134a refrigerant.
- Thermostat control accessible from inside enclosure.
- Hot gas bypass valve prevents evaporator freeze up while minimizing heavy inrush currents on large BTU/H units.
- Built in condensate evaporator.
- Continuous air circulation from high capacity fans.
- EMI/RFI suppression meets CE.
- Self-diagnostics on startup.
- Fault indication via LED light.
- Provision for door contact allowing power down when enclosure door is opened.
- Gasket, mounting kit and template for enclosure cutout and drilling are included.
- Condensate drain hose and clamp provided.
- Q Mount allows unit to hang in place for easy installation.

Accessories

- Gasket Kits
- Filter Kits
- Condensate Bottle
- Remote Door Switches
- Water Condensate Evaporator


DTS 3141



Front View




Side View



Drilling Template


DTS 3241



Front View



Side View



Drilling Template

Part No.	Ship Wt. lbs
DTS3141A115LG	99
DTS3141A230LG	99
DTS3241A115LG	127
DTS3241A230LG	127

Electrical Data	DTS3141A115LG	DTS3241A115LG
	DTS3141A230LG	DTS3241A230LG
Rated Voltage	115 V 60 Hz/ 230 V 50/60 Hz	115 V 60 Hz/ 230 V 50/60 Hz
Range of Operation	103-127 V/198-252V	103-127 V/198-252 V
Power Consumption	950 W/860 W	1400 W/1400 W
Running Amps	7.2 A/4.0 A	14.6 A/6.3 A
Starting Current	17.1 A/9.3 A	26.8 A/16.5 A
Line Cord	Terminal Block	Terminal Block

Refrigeration Data	DTS3141A115LG DTS3141A230LG	DTS3241A115LG DTS3241A230LG
Rated Capacity	4,000 BTU/H (1,172 Watts)	7,500 BTU/H (2,197 Watts)
Type of Refrigerant	R134a	R134a
Refrigerant Charge	500 g	500 g
Adjustable Thermostat	Factory setting +95°F (+35°C)	Factory setting +95°F (+35°C)

	DTS3141A115LG	DTS3241A115LG
Refrigeration Data	DTS3141A230LG	DTS3241A230LG
Max. Ambient Air Temp.	+125°F (+52°C)	+125°F (+52°C)
Min. Ambient Air Temp.	+46°F (+8°C)	+46°F (+8°C)
Air Capacity (unrestricted)	Internal Circulation 350 CFM	Internal Circulation 580 CFM
	External Circulation 350 CFM	External Circulation 580 CFM
Condensation Discharge	Condensate Evaporator	Condensate Evaporator
Filter Mat	Filterless	Filterless
Db Noise Level	<70 dB(A)	<73 dB(A)
Unit Weight	80 lbs (36 kg)	101 lbs (46 kg)
Exterior Case	Galvanized sheet metal	Galvanized sheet metal
Finish	RAL7035 Light Grey powder Finish	RAL7035 Light Grey powder Finish
NEMA Rating	Enclosures IP 54/NEMA 12	Enclosures IP 54/NEMA 12

Data subject to change without notice