


Farnell NO.	8706646	8706654	8706662
L ± T (mm)	500 ± 5	1000 ± 10	2000 ± 20
Farnell NO.	8706670	8706689	8706697
L ± T (mm)	3000 ± 30	5000 ± 40	10000 ± 70




SIDE:A

SIDE:B

NOTE:

- (1). Cable Wiring: CAT. 5E UTP Stranded 24AWG(7*0.18CU)*4P
Jacket Material:LSOH OD:5.0 ± 0.20mm
Cable Colour:GREY
Cable Printing: System Cable UTP CAT 5E 4 Pairs 24AWG
Stranded ISO 11801 100MHz
- (2). Connector A&B: RJ45(8P8C) Male Type
INSULATION:Clear Polyester
CONTACTS:Brass,Gold Plated
- (3). Over Mold: PVC, GREY
- (4).Parameter Settings: UT8080M
1. Conductive Resistance:1kΩ
2. Insulative Resistance:5MΩ (Min.)
- (5). Packing: POLYBAG PACKING

SIDE:A 8P8C		SIDE:B 8P8C	
1	ORANGE	1	ORANGE
2	WHITE/ORANGE	2	WHITE/ORANGE
3	GREEN	3	GREEN
6	WHITE/GREEN	6	WHITE/GREEN
4	WHITE/BLUE	4	WHITE/BLUE
5	BLUE	5	BLUE
7	BROWN	7	BROWN
8	WHITE/BROWN	8	WHITE/BROWN



PIN OUT: (4)

PACKING: (5)

GENERAL TOLERANCES
(UNLESS SPECIFIED)

Pro-SIGNAL

LENGTH: X. ± 1

.X ± 0.2


.XX ± 0.10

ANGLE: X° . ± 1°

.X° ± 0° 30'

UNIT:mm

REV:0/A



NAME

CAT. 5E UTP CABLE(24AWG CU)

DRAWING

OVP

S. P. NO.

DWG. NO.

CHECK

P. O. NO.

PAGE

1/1

0	2011/12/20
REV	DESCRIPTION
DATE	