


Type	Size	Description	Part No.
Neon	T10 (T-3/4)	Miniature Screw Neon Lamp	(see table)



Drawing Not To Scale
All Dimensions In mm

PERFORMANCE DATA

Farnell Part No.	SLI Part No.	Colour (glow discharge)	Relative Brightness	Nominal Current mA	Design Operating Voltage	Built-in Series Resistor		Av. Life Hours (ac)
						100 ~ 120V (ac only)	220 ~ 250V (ac/dc)	
653883	8LR110	Amber-Red	Standard	0.5	100 ~ 120	82kΩ	—	50000
179204	8UHR110	Amber-Red	Ultra High	2.6	100 ~120	22kΩ	—	10000
140181	8UHR220	Amber-Red	Ultra High	2.6	220 ~ 250	—	68kΩ	10000
179205	8GR110	Green	High	1.8	100 ~120	33 kΩ	—	10000
140278	8GR220	Green	High	1.8	220 ~ 250	100kΩ	—	10000

NOTES:

- 1) E10/13 nickel-plated screw cap in accordance with IEC 61-1, (BS EN 60061-1), sheet 7004-22-x.
- 2) Metal base to be durably marked with part number and trademark.
- 3) Products rated at 50Vac and above shall conform to European standards and directives SI 1994/3260, 73/23/EEC and 93/68/EEC and display the CE mark on the packaging labels.