







パターン参考寸法 (マウント面)
RECOMMENDED DIM. FOR P.C. BOARD
MOUNTING PATTERN (REF.)

注記 NOTES.

- 嵌合相手: 53268 シリーズ
MATES WITH: 53268 SERIES
- ハウジングの底面 [G] からの金具及びターミナル半田付面のズレ量は
上方向0.1MAX. 下方向0.15MAX. とする。
MISALIGNMENT OF SOLDER TAIL TIP AND FITTING NAIL FROM [G]
: UPPER DIRECTION 0.1mmMAX.
: LOWER DIRECTION 0.15mmMAX.

3. パターンハブリ止メ用金具
FITTING NAIL FOR PREVENTION OF PEELING
OF P.C.B. PATTERN.
4. 本製品は52365-**-20の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52365-**-20.

3. 金具 FITTING NAIL
(リン青銅、
ニッケル下地 錫メッキ)
t=0.25
(PHOSPHOR BRONZE
TIN OVER NICKEL PLATING)
t=0.25

18.7	14	52365-3029	30
17.7	13	-2829	28
16.7	12	-2629	26
15.7	11	-2429	24
14.7	10	-2229	22
13.7	9	-2029	20
12.7	8	-1829	18
11.7	7	-1629	16
10.7	6	-1429	14
9.7	5	-1229	12
8.7	4	-1029	10
7.7	3	-0829	8
6.7	2	52365-0629	6
B	A	MATERIAL NO.	極数 CIRCUIT

EC NO.					REV	MATERIAL 材料	FINISH 仕上げ	WIRE RANGE 適用電線範囲	INS. RANGE 被覆外径	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE —#	MODEL NO. DESIGN UNITS ☑mm ☐INCH	DIMENSIONS: THIRD ANGLE PROJECTION ☐mm ☐INCH ☐mm ONLY	SHT REV
DRWN: CH'K: APPR:	DRWN: CH'K: APPR:	DRWN: CH'K: APPR:	DRWN: CH'K: APPR:	DRWN: CH'K: APPR:										
0					0	SEE DRAWING	—#	—#	—#	10 UNDER 未満	±0.2	52365-**-29	1.0 BOARD TO BOARD CONN. REC. HSG. ASS'Y SMT. -LEAD FREE-	1 OF 1
1					1					10 OVER 以上	±0.25			
2					2					30 UNDER 未満	±0.25			
3					3					30 OVER 以上	±0.3			
4					4					ANGLE 角度	±3°			
5					5					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				
6					6					SIZE B				

