

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300500251](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Brad RJ-Lnxx RJ-45 Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 24 AWG, PVC Cable, 1.0m (3.28') Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Industrial Cordsets
Series [130050](#)
Connector End A RJ-45 (industrial)
Connector End B RJ-45 (industrial)
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Industrial Ethernet Solutions](#)
Performance Category 5e
Product Name Brad, RJ-Lnxx
Protocol N/A
Region America, Asia, Europe
Type Double Ended
UPC 78678850100

Physical
Cable Diameter 6.35mm (.250")
Cable Length 1.0m (3.28')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Male-Male
Keyway None
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PUR
Material - Coupling Nut ASA
Material - Plating Mating N/A
Orientation Straight to Straight
Poles 8
Temperature Range - Operating -10°C to +60°C
Wire Size AWG 24
Wire/Cable Type Unshielded-Twisted Pair

Electrical
Current - Maximum per Contact 1.5A
Voltage - Maximum 30V

Material Info
Engineering Number ENQ3115M010

Reference - Drawing Numbers
Sales Drawing SD-130050-006



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130050](#) Series