


MATERIALS

BODY	PASSIVATED STAINLESS STEEL
CONTACT	GOLD PLATED
SUPPORT BEAD	AIR POLYPHENYLENE OXIDE COMPOSITE
COUPLING NUT	BRASS NICKEL PLATED



SPECIFICATIONS

FREQUENCY RANGE: DC TO 40 GHz

ATTENUATION: 10 dB

IMPEDANCE: 50 OHMS

ACCURACY: ± 1.0 dB

VSWR: 1.40:1 MAXIMUM

AVG. POWER HANDLING CAPABILITY: .5 WATT

*2.9mm CONNECTORS WILL MATE BOTH
ELECTRICALLY & MECHANICALLY WITH ALL SMA,
3.5mm & K CONNECTORS. THE K CONNECTOR
IS A TRADE MARK OF ANRITSU CORPORATION.*



PASTERNAK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: www.pasternack.com
E-MAIL ADDRESS: sales@pasternack.com

COAXIAL & FIBER OPTICS

DWG TITLE

PE7046-10

DES.

2.9mm ATTENUATOR, 10 dB FREQUENCY
RANGE: DC TO 40 GHz

SIZE A

FSCM NO. 53919

CAD FILE

042309

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.