

FIT® Preferred Heat Shrink Products

GENERAL PURPOSE, IRRADIATED POLYOLEFIN


FIT®-221

MIL-DTL-23053/5C,
CLASS 1, 2
UL STANDARD 224
CSA STANDARD 198
RoHS COMPLIANT

CHOOSE **FIT**®-221 For:

- General Purpose Protection and Repair
- Identification and Beautifying Substrates
- Insulation from Environment
- Reduced Longitudinal Shrinkage
- Resistance to Water, Fungus, UV Light (black only)
- Use with **XTRA•GUARD**® 1

2 to 1 SHRINK RATIO



FIT®-221 APPLICATIONS:

- General Purpose Insulation and Repair
- Wire and Cable Harnessing and Bundling
- Cable and Connector Protection
- Wire and Tubing Splicing and Connecting
- **XTRA•GUARD**® 1 Applications
- Automated Cutting Machines (spools)

CHARACTERISTICS

OPERATING TEMPERATURE:

- -55°C to 135°C

SHRINKAGE RATIO:

- Approximately 2 to 1 at 121°C

COLOR DESCRIPTION:

- 4-Foot Lengths:
3/64 to 2 Inch — Black, White, Clear, Red, Yellow, Blue, Green
3 and 4 Inch — Black, Clear
- 6-Inch Lengths:
3/64 to 1 Inch — Black, White, Clear, Red, Yellow, Blue, Green
1-1/2 to 3 Inch — Black, Clear
- 1/2 or 1 Inch Cut Pieces: Black
- Spools: See Color Availability Chart Next Page

PHYSICAL PROPERTIES:

- Tensile Strength: 1500 psi, (106 kg/cm²)
- Ultimate Elongation: 200%
- Longitudinal Shrinkage: -5%
- Specific Gravity: 1.35
- Secant Modulus: 2.5 x 10⁴ max.
- Flammability: Self-Extinguishing

CHEMICAL PROPERTIES:

- Corrosive Effect: Passes Copper Stability Test
- Fungus Resistance: No Growth

ELECTRICAL PROPERTIES:

- Dielectric Strength: 500V/mil (197 kV/cm)
- Volume Resistivity: 10¹⁴ ohm-cm

SPECIFICATIONS

- MIL-DTL-23053/5C, Class 1, 2
- UL Standard 224 (except for Clear)
- CSA Standard 198 (except for Clear)
- RoHS Compliant

 **Recognized Component**
Underwriters Laboratories Inc.

 **Certified**
Canadian Standards Association

 **RoHS Compliant**

Packaged Assortments

Assorted Sizes of 6" Lengths
Each Length – Size Identified
Assorted Colors

Alpha Part No.	Tubing Size Range	Lengths Per Box
FIT-221-MS-1	3/64" – 3/16" (5 Sizes)	6 per Size (30 Lengths)
FIT-221-MS-2	1/4" – 3/4" (4 Sizes)	4 per Size (16 Lengths)

Recommended For Use With
XTRA•GUARD® 1
Extra-Premium Grade PVC Jacketed
General Purpose Cables



MIL-DTL-23053/5C,
CLASS 1, 2
UL STANDARD 224
CSA STANDARD 198
RoHS COMPLIANT

FIT® Preferred Heat Shrink Products

GENERAL PURPOSE, IRRADIATED POLYOLEFIN

FIT®-221

Alpha Part No. And Size	Minimum Supplied I.D.		Maximum Recovered I.D.		Nom. Recovered Wall Thickness		4 Ft. Lengths Total Ftg.	Standard Packages			No. Cut Pieces 6 Inch	No. Cut Pieces 1/2" or 1"
	Inches	mm	Inches	mm	Inches	mm		Tot. Ftg.	Tot. Ftg.	Tot. Ftg.		
FIT-221-3/64	0.046	1,17	0.023	0,58	0.016	0,41	100	1000			40	1000
FIT-221-1/16	0.063	1,60	0.031	0,78	0.017	0,43	100	1000	100	70	36	1000
FIT-221-3/32	0.093	2,36	0.046	1,17	0.020	0,50	100	500	100	65	32	1000
FIT-221-1/8	0.125	3,18	0.062	1,58	0.020	0,50	100	500	100	60	28	1000
FIT-221-3/16	0.187	4,75	0.093	2,36	0.020	0,50	100	500	100	50	24	1000
FIT-221-1/4	0.250	6,35	0.125	3,18	0.025	0,63	100	250	100	40	20	1000
FIT-221-3/8	0.375	9,53	0.187	4,75	0.025	0,63	100	200	50	35	16	1000
FIT-221-1/2	0.500	12,70	0.250	6,35	0.025	0,63	20	150	50	32	14	-
FIT-221-3/4	0.750	19,10	0.375	9,53	0.030	0,76	20	250	50	24	12	-
FIT-221-1	1.000	25,40	0.500	12,70	0.035	0,88	20	250	50	16	8	-
FIT-221-1-1/2	1.500	38,10	0.750	19,10	0.040	1,02	20	125	-	-	5	-
FIT-221-2	2.000	50,80	1.000	25,40	0.045	1,16	20	125	-	-	3	-
FIT-221-3	3.000	76,20	1.500	38,10	0.050	1,27	8	100	-	-	2	-
FIT-221-4	4.000	101,60	2.000	50,80	0.055	1,40	8	50	-	-	1	-

SPOOL COLOR AVAILABILITY CHART

FIT-221 Tubing Size	Put-Up	Colors	FIT-221 Tubing Size	Put-Up	Colors
3/64"	1000'	Black, Clear	3/8"	200'	All Colors
1/16"	1000'	All Colors*	50'	Black, Clear	
	100'	Black, Clear	35'	All Colors	
	70'	All Colors	1/2"	150'	All Colors
3/32"	500'	All Colors	50'	Black, Clear	
	100'	Black, Clear	32'	All Colors	
	65'	All Colors	3/4"	250'	All Colors
1/8"	500'	All Colors	50'	Black, Clear	
	100'	Black, Clear	24"	All Colors	
	60'	All Colors	1"	250"	All Colors
3/16"	500'	All Colors	50"	Black, Clear	
	100'	Black, Clear	16"	All Colors	
	50'	All Colors	1-1/2"	125'	Black, Clear
1/4"	250'	All Colors	2"	125'	Black, Clear
	100'	Black, Clear	3"	100'	Black, Clear
	40'	All Colors	4"	50'	Black, Clear

*All colors include black, white, clear, red, yellow, blue, green