



### MATERIALS:

#### Retractable Sheath Banana Plug:

Plug Body: Brass, Nickel Plated.

Banana Plug Spring: Beryllium Copper.

Compression Spring: Stainless Steel

Tip: Nylon, Color Matches Color of Wire.

Insulation: Nylon Molded to the Plug Body and Wire. Color Matches Color of Wire.

Wire: 18 AWG, Stranding 65 x 36 t.c., PVC Insulated, .144 (3.66cm) O.D.

Marking: POMONA 5259-XX

Color: Referenced by Part Number.

#### In-Line Banana Jack:

Jack Body: Brass, Nickel Plated.

Insulation: Polypropylene Molded to the Jack Body and Wire. Color Matches Color of wire.

Marking: POMONA ELECTRONICS CALIF.

### RATINGS:

Operating Temperature: +55°C (+131°F) Max.

Operating Voltage: 1000 VRMS.

Operating Current: 10 Amperes Max.

### ORDERING INFORMATION: Model 5259-XX-\*

XX = Wire Length, Standard Lengths: 12" (30,48cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

\* = Color, -0 Black, -2 Red

Ordering Example: 5259-12-2 Patch Cord is 12" (30,48cm), Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5259-12-2](#) [5259-12-0](#) [5259-36-0](#) [5259-36-2](#) [5259-24-0](#) [5259-24-2](#) [5259-48-0](#) [5259-48-2](#)