



SANDVIK BELZER

VDE insulated
voltage testerFor slotted head
screws

Single pole voltage tester DIN 57680/6 and VDE 0680/6.

Finish: blade fine polished bright chrome-plated, entirely hardened, tip black oxidized, clear transparent plastic handle.**Material:** blade of VANADIUM-EXTRA. Handle of cellulose acetate, impact resistant.

Up to 250 V alternation voltage to earth.

To test, hold the tip of screwdriver blade against the conductor and place a finger on the contact electrode at the upper end of the plastic handle. When voltage is present the glow tube in the handle will light up.

8045VDE



Product code	EAN code						
	731415+		mm	mm	mm	mm	g

8045VDE	1317256	10	0,5	3,5	77	14x92	170	40
---------	---------	----	-----	-----	----	-------	-----	----



8045LVDE



Light model with round handle and clip.

Product code	EAN code						
	731415+		mm	mm	mm	mm	g

8045LVDE	1509163	10	0,5	3,5	42	16x90	134	20
----------	---------	----	-----	-----	----	-------	-----	----



Voltage tester

150 - 250 volts, nickel-plated CHROME-VANADIUM blade. Insulated to the tip. With clip and control lamp.

806



Product code	EAN code						
	731415+		mm	mm	mm	mm	g

806-1-1	8003760	6	0,6	3	65	15x75	140	30
---------	---------	---	-----	---	----	-------	-----	----

