


PART NO. SEE CHART
Dwg. NO. SD-92315-001



90327 CONNECTOR	
CIRCUIT SIZE	DIMENSION W
4	7.59
6	10.13
8	12.67
10	15.21
12	17.75
14	20.29
16	22.83
18	25.37
20	27.91
22	30.45
24	32.99
26	35.53

CABLE DETAILS:

28 AWG , 1.27 MM PITCH , 7 STRANDS WITH TINNED COPPER ,
GREY PVC INSULATION WITH A COLOURED POLARITY STRIPE
INDICATING CIRCUIT NO. 1 , UL 2651.

ORDERING INFORMATION

92315-****

CIRCUIT SIZE
LENGTH L IN CENTIMETRES

LENGTHS AVAILABLE FROM 6 CM TO 120 CM

e.g. 92315-1208 = 12 CIRCUIT
WITH LENGTH L OF 8 CM.

NOTE : FOR LENGTHS OF
100 CM , THE PART NO. IS 92315-***01
105 CM , THE PART NO. IS 92315-***02
110 CM , THE PART NO. IS 92315-***03
115 CM , THE PART NO. IS 92315-***04
120 CM , THE PART NO. IS 92315-***05

NOTES:

1. SEE PRODUCT SPECIFICATIONS PS-99020-0011.
2. SEE TERMINATION SPECIFICATION ES-99033-0001.
3. SEE CABLE SPECIFICATION ES-99027-0006.
4. HARNESSES WILL BE 100% ELECTRICALLY TESTED FOR
SHORTS AND DISCONTINUITIES.

ADDED OPTION EC NO. 2002-1088 DRAWING NO. 020607 CHK: / / APPR: / /		QUALITY SYMBOLS MAJOR = CRITICAL =	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 4 : 1	DESIGN UNITS ☒ mm ☐ INCH	THIRD ANGLE PROJECTION 	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY		SHT	REV
			mm	INCH	DRAWN BY & DATE MCURRAN 98/06/19	CHECKED BY & DATE AMcCANN 98/06/19		TITLE: PICO FLEX IDT TO IDT STANDARD ASSEMBLIES		REVISE ON CAD ONLY	
4 PLACES ±0.			±.		APPROVED BY & DATE MWILHITE 98/06/19		MATERIAL NO.		DRAWING NO.		SHEET NO. 1 OF 1
3 PLACES ±0.			±.		CAD FILENAME S92315X1.DGN		SEE CHART		SD-92315-001		
2 PLACES ±0.			±.		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		SIZE B		
1 PLACE ±0.			±.								