



Technical Data

3M™ Chemical Sorbents

Use

For control of spills of certain hazardous liquids.

Product Description

3M™ Chemical Sorbents are made from inert, synthetic fibers principally polypropylene and polyester. They are available in a wide range of formats and are lightweight and nominally dust-free. They have a high adsorption capacity which minimizes the amount of waste for disposal.

Color

Highly visible. Yellow (High Capacity pads and rolls, P-110 pads), yellow with multi-colored material flecks (Medium Capacity pads and rolls). Mini-booms and pillows are white with black print. Medium Capacity appearance may vary due to recycle content used.

Selection Guide

- Folded – Combines four formats in one product. It is perforated every 16 inches (40 cm) and can be unfolded to be used as booms, pillows, sheets or rolls.
- Minibooms – Generally on-land applications to contain and adsorb spills.
- Pillows – Used for bulk absorption of oil on land or water. Particularly useful in drains to act as interceptors.
- Pads – A highly adaptable format. They can be used on water to pick up oil covering large surface areas and in wiping applications.
- Particulate – For fast coverage and adsorption of spills.
- Rolls – For fast coverage of large surface areas of water, they can be easily torn to length. Also used as a mat to keep shorelines or banks clean and to place used sorbents upon.
- Spill Kits and Response Packs – May contain different types of sorbents and temporary disposal bags. Compact for easy storage and quick response.

Typical Liquids Adsorbed

3M chemicals sorbents are suitable for adsorbing a wide range of liquids including certain acids, bases, coolants, petroleum based fluids, non-aggressive chemicals and aqueous based solutions.





Limitations of Use

3M recommends that a compatibility test with the liquid of interest be carried out prior to using the sorbent. For use in temperature over 60C it is essential that such a compatibility test is made prior to use. Do not use 3M chemical sorbents with the following concentrated chemicals as there is a risk of degradation: oleum, chlorosulfonic acid, liquid bromine, fuming nitric acid, chromic acid, sulfuric acid and hydrogen peroxide.

Precautions

3M chemical sorbents are not in themselves hazardous products, however, they take on the characteristics of the liquids they adsorb. Adequate precautions should be taken when handling or storing hazardous / flammable materials and appropriate personal protective equipment should be worn. Users should be informed of the risks incurred in use, storage and disposal of used sorbents.

Disposal

Dispose of used sorbents only in accordance with local and national regulations. Disposal companies should be consulted for their recommendations.

Waste Minimization

3M recommends that waste streams should be minimized wherever possible. 3M sorbents promote minimization by only being a small part of the total waste. In addition where laws allow, 3M sorbents can be disposed of by incineration yielding less than 0.2% ash (ASTM D-482). The high energy value of the sorbents is also favorable for incineration and waste-to-fuel systems.

Sustainability

High Capacity sorbents contain at least 25% recycled content by weight. Medium Capacity sorbents contain at least 50% recycled content by weight.

Adsorption / Sorbency

The sorbent capacity quoted in the table below is based on testing per ASTM F 726 "Standard Test Method for Sorbent Performance of Adsorbents." In brief, the sorbent samples were immersed in a "medium" density oil, drained and weighed. In the 1981 version of the standard, samples are immersed for a variable period of time in an attempt to make sure the sorbent is saturated. The sorbent is then drained horizontally. In the 2006 version of the standard, samples are immersed for 15 minutes and then most types are drained vertically. Capacity according to both versions of the standard is presented. **Data presented are nominal; there will be variability in sorbent performance.** Capacity and speed of adsorption will differ depending on the liquid's polarity, surface tension and viscosity. Ambient temperature may also affect results. Therefore, results will vary by application.



Product Number	Size	Number / Case	Case Shipping Weight lb (kg)	Nominal capacity per case ASTM F 726-81 gallons (liters)	Nominal capacity per case ASTM F 726-06 gallons (liters)
Folded					
C-FL550DD high capacity	5 in x 50 ft (12 cm x 15 m)	3	14 (6.4)	31.5 (119)	26.5 (100)
Minibooms					
P-200	3 in diameter x 4 ft (7.6 cm diameter x 121 cm)	12	13 (5.9)	12 (45)	14 (53)
P-208	4 in diameter x 8 ft (10.1 cm diameter x 243 cm)	6	13 (5.9)	12 (45)	14 (53)
P-212	4 in diameter x 12 ft (7.5 cm diameter x 365 cm)	4	13 (5.9)	12 (45)	14 (53)
Pillows					
P-300	7 in x 15 in (17 cm x 38 cm)	16	14 (6.4)	8 (30)	9.5 (36)
Pads					
C-PD914DD	9.5 in x 14.5 in (23.8 cm x 36 cm)	150	10 (4.5)	23.5 (89)	17.5 (66)
MCC medium capacity	15 in x 17 in (38 cm x 43 cm)	100	6 (2.8)	18 (68)	13.5 (51)
P-110	11 in x 13 in (28 cm x 33 cm)	200	14 (6.4)	17 (64)	13.5 (51)
Particulate					
P-500	NA	1	13 (5.9)	14 (53)	23 (87)
Rolls					
C-RL15150DD	15.25 in x 150 ft (39 cm x 45 m)	1	9 (4.1)	31 (117)	24 (91)
C-RL38150DD	38 in x 150 (96 cm x 45 m)	1	21 (9.5)	76 (287)	60.5 (229)
MCC medium capacity	15 in x 150 ft (38 cm x 45 m)	1	7 (3.1)	19 (72)	14 (53)
MCC medium capacity	25 in x 150 ft (63 cm x 45 m)	1	11 (5.1)	30 (114)	22 (83)
Spill Kits					
C-SKFL5	C-FL550DD at 26 ft (7.9 m)	3 rolls	7 (3.2)	15 (57)	13.5 (51)
C-SKFL31	C-FL550DD 17 in x 19 in (43 cm x 48 cm)	2 rolls 30 pads	18 (8.2)	31 (117)	26 (98)
SRP-Chem	P-200 P-110	9 mbms 30 pads	13 (5.9)	10.5 (40)	11 (42)



Important Notice to User:

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for user's particular purpose and suitable for user's method of application.

Warranty and Limited Remedy: 3M warrants that each 3M product will be free from defects in material and manufacture for 90 days from the date of purchase from 3M's authorized distributor. 3M MAKES NO OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a 3M product does not conform to this warranty, the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. **Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted.



Commercial Solutions Division
St. Paul, MN 55144-1000
1-800-852-9722
www.3M.com/facility

NSF and the mark are registered trademarks of NSF International.
3M and Scotch-Brite are trademarks of 3M Company.
Used under license in Canada.
© 3M 2015. All rights reserved.
Celum ID# 787228