

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

# PANDUIT INVENTORY NUMBERING SYSTEM

HSTTVA 12 - 48 - Q

PACKAGE QUANTITY: Q = 25  
S = 5

TUBE LENGTH IN INCHES

TUBING SIZE- EXPANDED I.D.

FLEXIBLE. ADHESIVE LINED THIN WALL HEAT SHRINK TUBING.

| PANDUIT<br>PART<br>NUMBER | Min.<br>Exp. I.D<br>In. (mm) | Max.<br>Rec. I.D<br>In. (mm) | NOMINAL REC<br>WALL THICKNESS<br>In. (mm) |
|---------------------------|------------------------------|------------------------------|-------------------------------------------|
| HSTTVA12                  | .125<br>(3.2)                | .063<br>(1.6)                | .021±.004<br>(.53±.102)                   |
| HSTTVA19                  | .187<br>(4.8)                | .093<br>(2.4)                | .023±.004<br>(.58±.102)                   |
| HSTTVA25                  | .250<br>(6.4)                | .125<br>(3.2)                | .029±.005<br>(.74±.127)                   |
| HSTTVA38                  | .375<br>(9.5)                | .187<br>(4.8)                | .029±.005<br>(.74±.127)                   |
| HSTTVA50                  | .500<br>(12.7)               | .250<br>(6.4)                | .030±.005<br>(.76±.127)                   |
| HSTTVA75                  | .750<br>(19.0)               | .375<br>(9.5)                | .035±.005<br>(.89±.127)                   |
| HSTTVA100                 | 1.000<br>(25.4)              | .500<br>(12.7)               | .042±.007<br>(1.07±.178)                  |
| HSTTVA150                 | 1.500<br>(38.1)              | .750<br>(19.0)               | .047±.008<br>(1.19±.203)                  |

## NOTES:

- SHRINK RATIO: 2:1
- SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S.
- MATERIAL: CROSSLINKED POLYOLEFIN WITH ADHESIVE
- COLOR: BLACK
- "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"

## DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

G00239K\_PB\_HSTTVA\_00

**PANDUIT**

CORP. TINLEY PARK, ILLINOIS

FLEXIBLE ADHESIVE LINED  
THIN WALL HEAT SHRINK  
(HSTTVA)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)  
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
LGRAVITT

MAT'L:

SCALE NONE

DATE  
5/14/03

SEE NOTES

DRAWING NO.

G00239KN

DWG  
A  
SIZE

|     |         |     |                 |             |         |      |     |
|-----|---------|-----|-----------------|-------------|---------|------|-----|
| R   | 5/14/03 | LGG | INITIAL RELEASE | G00239KN    | R       |      |     |
| REV | DATE    | BY  | CHK             | DESCRIPTION | ECN - R | CUST | SUP |