




- VDC: 12, 24
- RPM: 2800~9500
- CFM: 2.70~10.61
- Impeller: 5 blades

- Rotational direction CCW view from front face
- PBT94V-0 frame and impeller
- AWG 26; UL 1007 lead wires
- Mass: 36g




DC FAN

40x40x20mm

Specification

	Bearing	Voltage	Current	Speed	Input Power	Air Flow	Static Pressure	Noise	Weight
MODEL NO	○ Sleeve ● One ball and one sleeve ○ Hydraulic	(Vdc)	(Amp)	(Rpm)	(Watts)	(CFM)	(mm/H ₂ O)	dB(A)	Gram
B4020B12L	●	12	0.07	5000	0.84	5.43	3.35	25.3	36
B4020B12M	●	12	0.13	6500	1.56	7.01	5.90	30.9	36
B4020B12H	●	12	0.17	8000	2.04	9.33	9.31	33.9	36
C4020B12L	●	12	0.07	5000	0.84	5.43	3.35	25.3	36
C4020B12M	●	12	0.13	6500	1.56	7.01	5.90	30.9	36
D4020B12L	●	12	0.08	5000	0.96	5.43	3.35	25.3	36
D4020B12M	●	12	0.13	6500	1.56	7.01	5.90	30.9	36
D4020B24M	●	24	0.05	6500	1.20	7.01	5.90	30.9	36
D4020B24U	●	24	0.10	9500	2.40	10.61	12.21	37.8	36
E4020B12H	●	12	0.05~0.165	2800~9000	0.6~1.98	2.70~9.84	1.07~11.31	23.0~39.2	36
F4020B12L	●	12	0.07	5000	0.84	5.43	3.35	25.3	36
F4020B12M	●	12	0.10	6500	1.20	7.01	5.90	30.9	36
F4020B12H	●	12	0.17	8600	2.04	9.83	10.59	34.2	36
F4020B12U	●	12	0.25	9500	3.00	10.61	12.21	37.8	36

Design specifics subject to change without notice.



STATIC PRESSURE

