molex
one company > a world of innovation

Part Number: 89999-3185

Series image - Reference only

Status:	Inactive
Series:	87437
Category:	PCB Headers
Old Part Number:	87437-0533 REV A4

Mates With Part(s):
87439

Part Detail

General

Status	**Inactive**
Category	PCB Headers
Series	87437
Application	Signal, Wire-to-Board

Physical

Breakaway	No
Durability (mating cycles max)	10
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel, Tube
Pitch - Mating Interface	1.50mm
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55°C to +105°C

Electrical

(Please review the Product Specification for specific details.)	
Current - Maximum per Contact	3A
Voltage - Maximum	350V

Material Info

Old Part Number	87437-0533 REV A4

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part