





|                              |                                 |
|------------------------------|---------------------------------|
| <b>Rating</b>                | 21A 14VDC                       |
| <b>Contact Resistance</b>    | 50m ohm Max.                    |
| <b>Insulation Resistance</b> | DC 500V 100M ohm Min.           |
| <b>Dielectric Strength</b>   | AC 1500V 1 minute               |
| <b>Operation Temp.</b>       | - 20° C ~ 85° C                 |
| <b>Function</b>              | 3P SPST ON - OFF Lamp Dependent |
| <b>Lamp Type</b>             | LED 12VDC 14V w/resistor        |

| Mounting Hole                                                                      |                                                                            |                                                                           | Circuit Diagram                                                                                          |
|------------------------------------------------------------------------------------|----------------------------------------------------------------------------|---------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------|
|  |                                                                            |                                                                           |  <p>12V R=680 ohm</p> |
| Thickness                                                                          | X                                                                          | Y                                                                         |                                                                                                          |
| 0.75~5mm<br>0.03~0.2inch                                                           | 36.8 <sup>+0.2</sup> <sub>-0</sub><br>1.45 <sup>+0.008</sup> <sub>-0</sub> | 15.3 <sup>+0.2</sup> <sub>-0</sub><br>.60 <sup>+0.008</sup> <sub>-0</sub> |                                                                                                          |



Material:  
 Frame: Black, Nylon# 66  
 Actuator: Black, Nylon#66+33%GF  
 Lens: Red, PC  
 Printed: None  
 Water proof and dust proof to fit IP-56



RoHS Compliant

2 Added Dependent to function & Lamp Type. 12/08/11.  
 1 Rotated button and updated views & Circuit diagram. 1/13/11.

**CW INDUSTRIES**  
 Southampton, Pa. 18966  
 Tel 215.355.7080/www.cwind.com

Date Drawn: 12/08/10

Rev. 2

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB258B01BR1**