


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982660262](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 178.00mm Cable Length, Tin (Sn) Plating, 24 Circuits



Documents:
[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification PS-98266-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-98266-001-001 \(PDF\)](#)

General
Product Family Cable
Series [98266](#)
Comments Contacts on opposite sides, Type D
Crimp Quality Equipment Yes
Overview [Premo-Flex Cable Jumpers](#)
Product Name Premo-Flex FFC Jumper
UPC 756054772096

Physical
Cable Length 178.00mm
Circuits (Loaded) 24
Material - Plating Mating Tin
Net Weight 1.383/g
Packaging Type Bag
Pitch - Mating Interface 0.50mm
Temperature Range - Operating -40° to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 0.5A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-98266-001-001
Product Specification PS-98266-001-001
Sales Drawing SD-98266-001

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed
For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[98266 Series](#)

Mates With
Easy-On FFC/FPC Connector:

[524352433](#) , [524372433](#) , [5019512400](#) ,
[525592433](#) , [525592 434](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION