



**VG95234 KR**  
**Receptacle Protective Cover**  
**With Stainless Steel Chain**



| DIMENSIONS     |        |            |        |        |                |
|----------------|--------|------------|--------|--------|----------------|
| Connector Size | D1 Max | D2 +0.6 -0 | L1 Min | L2 Max | Weight gr. Max |
| 10 SL          | 23.5   | 4.3        | 90     | 15.5   | 16             |
| 14 S           | 30.5   | 4.3        | 90     | 15.5   | 18             |
| 16 S           | 33.0   | 4.3        | 90     | 15.5   | 19             |
| 16             | 33.0   | 4.3        | 100    | 21.2   | 23             |
| 18             | 37.5   | 4.3        | 100    | 21.2   | 27             |
| 20             | 41.0   | 4.7        | 115    | 21.2   | 30             |
| 22             | 44.0   | 4.7        | 115    | 21.2   | 33             |
| 24             | 47.5   | 4.7        | 115    | 21.2   | 37             |
| 28             | 54.5   | 4.7        | 160    | 21.2   | 42             |
| 32             | 61.0   | 5.5        | 160    | 21.2   | 48             |
| 36             | 67.5   | 5.5        | 160    | 21.2   | 55             |

**APPLICATION NOTES**

1. Metal protective cover for bayonet receptacle connectors with stainless steel chain.
2. Standard materials configuration consists of aluminum alloy with cadmium olive drab passivation IAW QQ-P-416.
3. Other types of front and rear connector accessories are available. See our website and/or contact the factory for complete information.