

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19071-0281

Status:

Active

Overview:

Solderless Terminals

Description:

InsulKrimp™ Ring Tongue Terminal for 2 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-009 (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19071

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Solderless Terminals

Product Name

InsulKrimp™

Type

Ring

UPC

800753072558

Physical

Barrel Type

Closed

Color - Resin

Red

Flammability

94V-0

Insulation

PVC

Material - Plating Mating

Tin

Net Weight

15.459/g

Packaging Type

Bag

Stud Size

1/4" (M6)

Wire Insulation Diameter

16.50mm max.

Wire Size AWG

2

Material Info

Old Part Number

G-675-14X

Reference - Drawing Numbers

Product Specification

PS-19902-009, PS-19902-011, PS-19902-013

Sales Drawing

SD-19071-005




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19071Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Hand Crimp Tool	0640013900
Die Set (large) for the HHLS Hydraulic Crimper	0192890010
Manual Putt Pump Hydraulic System, Die set required	0192860117
Hand Crimp Tool for 2 AWG Insulated Ring Terminals	0640017970

This document was generated on 12/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION