

RAD-PIG-EF316-N-SMA

Order No.: 2867694



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867694>

Adapter cable, pigtail 30 cm N (female) -> SMA (male), insertion
attenuation 1.5 dB at 2.4 GHz; impedance 50 ohms;

Commercial data

GTIN (EAN)	 4 017918 939069
sales group	H178
Pack	1 pcs.
Customs tariff	85442000
Catalog page information	Page 623 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
09/03/2007



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General

Connection 1	Plug connector connection
Type of connection	Type N (female)
Connection 2	Plug connector connection
Type of connection	Type SMA (male)
Fixed cable length	30 cm

Cable type	EF 316
Cable, attenuation	approx. 1.5 dB/m
Minimum bending radius	12.50 mm
External diameter	2.50 mm
Outer sheath, material	Radox (LSFH)
Connection name	Plug connector connection
Type of connection	Type N (female)
Ambient temperature (operation)	-40 °C ... 70 °C

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;