ED1100/X (5.0 mm)
EDZ1100/X (5.08 mm)



2-20 (16) poles, Spacing 5.0 mm or 5.08 mm
insert required no. of poles **x**
How to order see page 5

Ratings:			
Rated Voltage	**300 V**	**300 V**	**250 V**
Rated Current	**15A**	**12 A**	**12 A (T60)**
Wire Size	**AWG 22-10**	**AWG 22-10**	**2.5 mm²**
Rating Impulse Voltage/Dirt Level			**4 kV/3**
Rated Torque/ScrewSize			**0.5 Nm/M3**
Max. Rated Cross Section			
Single Wire (solid)			**2.5 mm²**
Stranded Wire (flexible)			**2.5 mm²**
Stranded wire with Ferrules			**2.5 mm²**
Dimensions			
Spacing			**5.0 mm (5.08 mm)**
Stripped Length			**7.0 mm**
Materials			
Insulating Material			**PA**
Flammability Class			**UL94 V-0**
Temperature Range			**-30˚C/+105˚C**
Terminal Block			**CuZn**
Contact			**CuSn**
Color			
Green